

Automation Accessories

90° Transfer Plate



| Conveyor Width | Part No. |
|----------------|-------------|
| 2 in. | 125-0230-02 |
| 3 in. | 125-0230-03 |
| 4 in. | 125-0230-04 |
| 6 in. | 125-0230-06 |
| 8 in. | 125-0230-08 |
| 10 in. | 125-0230-10 |
| 12 in. | 125-0230-12 |
| 18 in. | 125-0230-18 |
| 24 in. | 125-0230-24 |

Notes:

Transfer plates are not intended for use with high friction or cleated belts.

Discharge conveyor must be pushing.

Customer to drill screw holes to mount plate.

Inline Transfer Plate



| Conveyor Width | Part No. |
|----------------|-------------|
| 2 in. | 125-0220-02 |
| 3 in. | 125-0220-03 |
| 4 in. | 125-0220-04 |
| 6 in. | 125-0220-06 |
| 8 in. | 125-0220-08 |
| 10 in. | 125-0220-10 |
| 12 in. | 125-0220-12 |
| 18 in. | 125-0220-18 |
| 24 in. | 125-0220-24 |

Note:

Transfer plates are not intended for use with high friction or cleated belts.

Pivot Mount Set



Note:

The pivot mount attaches to the tail end of the conveyor and enables a pivot point from which other devices can lift the conveyor. Includes left and right hand mount.

To Order:

Part No. 125-0172-00

Custom Rolling Nosebars



Note:

The rolling nosebar can be used with a conveyor running less than 60 fpm and carrying less than 5 lbs. per inch of conveyor width.

To Order:

Please denote an 'SAF' in the belt portion of the conveyor part number, and an 'R' for the tail pulley part of the conveyor part number.

Example: 1ESBH04-048-ASR-SAF

Adjustable Stops



To Order:

1. Select an adjustable stop for 1" sides, 2" sides, or single tee slot (See pages 22 -24)


2. Using the chart below, fill in the part number using the nominal width of the conveyor for the last two digits of the part number

| | Part No. |
|-----------------|-------------|
| 1" Sides | 125-0232-WW |
| 2" Sides | 125-0234-WW |
| Single Tee Slot | 125-0233-WW |

Example: 125-0232-04

End Stop for a 4" wide conveyor that has 1" aluminum side rails with wear strip

Adjustable Diverters



Note:

The adjustable diverter comes with a 5' piece of UHMW rail and (2) mounting assemblies that the user can utilize to help orient the product around a 90° transfer.

To Order:

Part No. 125-0250-000